

FAP stainless steel molds



FAP metal molds are made of high quality stainless steel.
Using FAP stainless steel molds:

- Extreme long life cycle,
- Very cost efficient,
- Wide range of molds available.



Article 4123-101
300 x 300 x 50 mm



Article 4123-102
195 x 195 x 28 mm



Article 4123-103
295 x 295 x 33 mm



Article 4123-104
215 x 215 x 30 mm



Article 4123-105
275 x 275 x 20 mm



Article 4123-106
275 x 275 x 48 mm



Article 4123-107
325 x 325 x 57 mm



Article 4123-108
245 x 245 x 23 mm



Article 4123-109
315 x 315 x 65 mm



Article 4123-110
225 x 225 x 70 mm



Article 4123-111
360 x 360 x 29 mm



Article 4123-112
218 x 218 x 16 mm



Article 4123-113
270 x 270 x 23 mm



Article 4123-114
305 x 305 x 23 mm

FAP stainless steel molds



FAP Stainless Steel Molds



Article 4123-115
348 x 348 x 29 mm



Article 4123-116
338 x 338 x 12 mm



Article 4123-117
275 x 275 x 14mm



Article 4123-118
207 x 207 x 15 mm



Article 4123-201
460 x 360 x 24 mm



Article 4123-202
220 x 115 x 19 mm



Article 4123-203
460 x 350 x 20 mm



Article 4123-204
360 x 235 x 19 mm



Article 4123-205
355 x 175 x 23 mm



Article 4123-206
320 x 130 x 18 mm



Article 4123-207
175 x 135 x 20 mm



Article 4123-208
195 x 135 x 30 mm



Article 4123-209
285 x 145 x 21 mm



Article 4123-301
470 x 145 x 23 mm



Article 4123-302
510 x 250 x 48 mm



SCHREIBER

Farb- und Antikglas

FAP stainless steel molds



Article 4123-303
135 x 100 x 26 mm



Article 4123-304
475 x 295 x 30 mm



Article 4123-305
410 x 215 x 20 mm



Article 4123-306
470 x 160 x 55 mm



Article 4123-401
293 x 293 x 23 mm



Article 4123-402
270 x 270 x 20 mm



Article 4123-403
205 x 205 x 12 mm



Article 4123-404
350 x 350 x 19 mm



Article 4123-405
310 x 310 x 46 mm



Article 4123-406
225 x 225 x 55 mm



Article 4123-407
265 x 265 x 65 mm



Article 4123-408
165 x 165 x 30 mm



Article 4123-409
145 x 145 x 11 mm



Article 4123-410
280 x 280 x 13 mm



Article 4123-411
225 x 225 x 12 mm



Article 4123-412
330 x 330 x 10 mm



Article 4123-413
300 x 300 x 10 mm



Article 4123-414
130 x 130 x 18 mm



Article 4123-601
335 x 335 x 52 mm



Article 4123-602
315 x 315 x 34 mm



Article 4123-603
245 x 245 x 23 mm



Article 4123-604
330 x 230 x 15 mm



Article 4123-605
370 x 218 x 16 mm



Article 4123-606
330 x 310 x 25 mm



Article 4123-501
575 x 575 x 195 mm



Article 4123-502
520 x 520 x 185 mm



Article 4123-503
550 x 550 x 250 mm



Article 4123-504
600 x 500 x 200 mm



Article 4123-505
630 x 520 x 190 mm



manual FAP stainless steel molds

FAP stainless steel molds are made of high quality stainless steel. Our molds are available in a wide variety of different sizes and shapes and have very low surface impurities. In our selection of molds you can find for example plates, platters and washbasins.



Preparing the mold

Before using the FAP stainless steel mold you have to "coat" the mold with kiln wash or shelfprimer to avoid the glass sticking to the mold.

We recommend to apply the kiln wash or shelfprimer when the mold is hot. This way the water vaporises and the primer will stick to the surface of the mold (instead of flowing to the bottom of the mold). For the best results, you can repeat this process a few times. When the mold is cooled, you can lightly rub the surface for a smooth finish.

We believe that the best way to apply the shelfprimer or kilnwash to the surface of the mold is using an airbrush or atomizer. This way the primer will be equally spread over the surface of the mold. Of course you can also use a big (paint)bush for this process.

